

Falling Dar

Instrument to determine the resistance of plastic film composite films, wrapping and other foods packages a packages, as well as alumin aluminum plastic compos

The instrument features for operation. The sampl released by means of

clamp. This instrument is suitable for tests according to method A, as well as method B, and includes both darts and weight sets.



Features

- Easy operation, automatic data processing
- Pneumatic clamping and magnetic dart release

and

Technical details

Range

Mains

50-2000 g (A) 300-2000 g (B) Precision 0.1 g 150 x 150 mm min Sample Pneumatic Clamping Dimensions 51 x 44 x 130 cm Weight 50 kg 220 V/50Hz

Standards

ISO 7765-1 · ASTM D1709

© +31 36 26 000 16

⊠ info@jarp.nl

